

USBPHP-S1 USB Programmable Single Channel Instrumentation Amplifier, and High Pass Filter

USB 2.0 compatible communication for setup and control
Non-volatile configuration retains all settings through power cycles
Does not need to be attached to a PC to operate
AC/DC converter included for 115VAC or 220VAC power
Optional 9 to 12V battery operation
Compatible with any 12-, 16, or 24-bit A/D converter device

Differential or single ended input with software selectable amplifier gains of 1 to 1000

 $\pm\,10V$ max Signal Input and Output with input protection up to $\pm40V$ Filter rejection band attenuation up to -90dB

High Pass Filter available as 4-pole Butterworth or Bessel.

High Pass Software select any Corner Frequency (Fc) from 10Hz to 1275Hz in HyN model (1100Hz to 41.5kHz in -HyE model)

Use multiple USBPHP-S1 units for multi-channel applications Windows 7/Vista/XP compatible menu setup software

Adaptable to most applications in the field, on the factory floor, or in the lab

The USBPHP-S1 stand alone USB controllable module provides a single channel of high pass filtering and high-quality instrumentation amplifier for front-end signal conditioning compatible with all popular A/D converter devices.

The USBPHP-S1 is powered with 9 to 12VDC so it can be connected to a battery voltage source or the supplied 115-220VAC adapter may be used for operation with wall power anywhere in the world.

When programmed from the USB port, the USBPHP-S1 will remember all of the programmed properties between power cycles. Program once and operate as a standalone signal conditioner without having to reprogram for every use. This is perfect for turn-key applications.

It's easy to connect the USBPHP-S1 into the data collection system. Input and output signals can be routed through BNC connection or using the detachable screw terminal connectors. Optional SMA type adapters are also available.

Protection from high input voltages

The USBPHP-S1 provides strong input protection and can withstand up to +/-40V at the analog signal input.

Amplify to improve signal resolution

The USBPHP-S1 high-quality instrumentation amplifier provides software-selectable gain as well as differential



inputs with high-common mode rejection. Gain can be set at 1, 2, 5, 10, 20, 50, 100, 200, 500 or 1000. The USBPHP-S1 Instrumentation Amplifier provides an excellent common-mode rejection of 90 to 100 dB typical at high gains.

Multiple unit operation individually software select any high corner frequency

Each USBPHP-S1 module in a multi-channel data collection system can have a unique filter characteristic, a unique set of corner frequencies, and a unique amplification.

All Software is Included

The USBPHP-S1 comes with a complete menu-driven program.

SystemViewUSBPxx is a ready-made Windows 7/Vista /XPcompatible application that uses a few simple mouse clicks to program the parameters of each USBPHP-S1 connected to the PC. Once selected, the desired parameters are set and saved to non-volatile memory in the USBPHP-S1 so that they are reapplied after every subsequent power up.

An ActiveX control is provided for custom software development. The COM interface of the ActiveX control can be integrated into any high level language application.

Alligator Technologies

Ordering information

USBPHP-S1/yz

y = high pass characteristic

z = high pass range

High Pass Filter Options

4-pole Butterworth y = B4-pole Bessel y = L

High Pass Range Options

Normal range z = NContinuously tunable from 10Hz to 1275Hz Extended range z = EContinuously tunable from 1100Hz to 41.5kHz Maximum pass band range 100kHz

Instrumentation Amplifier Stage

......@200-1000 0.3% max CMRR75dBmin, 86dB typ. at gain of 1

Common Mode Voltage+/-10V max

Input Voltage+/-10V max at gain of 1

Input Protection+/-40V max, with power off or on Input Impedance20M Ω differential (10M Ω each side to

analog ground)

DC offset, Factory Adjusted..<±.1.5mV DC offset vs. temperature.....<±20 μ V/°C DC offset, long term drift......<±5 μ V/Month Output impedance.....<0.01 Ω

Channel to Channel Phase matching

End user phase match calibration by varying HPFc can result in channel to channel phase match as small as

......0.23° at target pass band frequency

Physical

Number of channels1

Size 108mm(4.25")x83mm(3.25")x28mm(1.125")

Power consumption500mA at +9VDC Operating temperature......0°C to 70°C

Software

SystemViewUSBPxx.....Windows OS/XP and above

System Accessories

Connectors

USBPxx-S1/STA Screw terminal adapter kit(one 2-lead

STA and two 3-lead STA)

USBPxx-S1/SMAM two BNC to SMA Male adapters

USBPxx-S1/SMAF two BNC to SMA Female adapters

Power Adapters

P9V500MA Universal to 9V DC 500mA

PAP-NA Power Adapter Plug Furane

PAP-EUPower Adapter Plug EuropePAP-ASPower Adapter Plug Australia

USBPxx-S1/DCR DC regulator for 9 to 30VDC sources